



CTSS250700PC304L, 304 Stainless Steel Cable Tie, 250 Lb Tensile, 27.56" Long, Partially Coated

By Burndy
Catalog # [CTSS250700PC304L](#)

Semi coated stainless steel cable ties 304 grade, Tensile strength: 250 Lb, 27.56" L, 0.31" W, 7.09" Bundle Dia.

Features

- Stainless Steel Cable Tie - Partially Coated

General

Catalog Number	CTSS250700PC304L
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	270
Trade Name	UNIRAP™
UPC	781810647554
UPC 14 Digit GTIN	00781810647554

Dimensions

Dimension - Bundle Diameter	7.09
Max inch	

Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	50

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS250700PC304L](#)