



CTSS450500FC304L, 304 SS Tie, 450 Lb,
5" Bundle, Full Coat

By Burndy
Catalog # [CTSS450500FC304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 450 Lb. Tensile Strength
(Fully Coated)

Features

- Stainless Steel Cable Tie - Fully Coated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	FULLY COATED
----------------	--------------

Dimensions

Package Height	1.500 in
Length	19.68 in
Package Weight	2.560 lb.
Dimension - Width mm	12.7 mm
Dimension - Width inch	0.50 in
Package Length	24.000 in
Package Width	6.000 in
Dimension - L Length Overall mm	500 mm
Width	0.5 in
Dimension - Length Overall inch	19.68 in

Dimension - Bundle Diameter Max inch	5.04
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	450
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810647127
Material	304 STAINLESS STEEL
UPC 14 Digit GTIN	00781810647127

Logistics

Pallet Quantity	30000
Carton Quantity	1000

Operational

Operating Temperature Celcius Max	115 °C
Operating Temperature Range Celcius	-40 - 115
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)