



CTSS500400304L, 304 SS Tie, 500 Lb
Tensile, 15.75" Long

By Burndy
Catalog # [CTSS500400304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 500 Lb. Tensile Strength
(Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Package Height	0.900 in
Length	15.75 in
Package Weight	0.880 lb.
Dimension - Width mm	7.9 mm
Dimension - Width inch	0.31 in
Package Length	20.250 in
Package Width	4.250 in
Dimension - L Length Overall mm	400 mm
Width	0.31 in
Dimension - Length Overall inch	15.75 in

Dimension - Bundle Diameter	4.02
Max inch	

Force Related

Rating - Minimum Tensile Strength lbs	500
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651445
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810651445

Logistics

Minimum Pack Quantity	50
Pallet Quantity	80000
Carton Quantity	2200

Operational

Operating Temperature Celcius	300 °C
Max	
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius	-40 °C
Min	
Operating Temperature Range Fahrenheit	-

Product Assets

[Catalog \[English\]](#)