



CTSS500500304L, 304 SS Tie, 500 Lb
Tensile, 19.68" Long

By Burndy
Catalog # [CTSS500500304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 500 Lb. Tensile Strength
(Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Length	19.68 in
Dimension - Width mm	7.9 mm
Dimension - Width inch	0.31 in
Dimension - L Length Overall mm	500 mm
Width	0.31 in
Dimension - Length Overall inch	19.68 in

Dimension - Bundle Diameter Max inch	5.04
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	500
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651452
Material	304 STAINLESS STEEL
UPC 14 Digit GTIN	00781810651452

Logistics

Carton Quantity	1900
-----------------	------

Operational

Operating Temperature Celcius Max	300 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Fahrenheit	-

Product Assets

[Catalog \[English\]](#)