



CTSS675200FC304Q, 304 Stainless Steel Cable Tie, 675 Lb Tensile, 7.87" Long, Fully Coated

By Burndy
Catalog # [CTSS675200FC304Q](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 675 Lb, 7.87" L, 0.62" W, 1.97" Bundle Dia.

Features

- Stainless Steel Cable Tie - Fully Coated

General

Catalog Number	CTSS675200FC304Q
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	675
Trade Name	UNIRAP™
UPC	781810647165
UPC 14 Digit GTIN	00781810647165

Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm

Dimension - Length Overall inch	7.87 in
Dimension - Width inch	0.62 in
Dimension - Width mm	15.9 mm

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	25

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
[Sales Drawings - 50020256](#)
[Specifications - CTSS675200FC304Q](#)



A Hubbell brand