



CTSS675400PC304Q, 304 SS Tie, 4" Bundle, Partial Coat

By Burndy
Catalog # [CTSS675400PC304Q](#)

304 Stainless Steel UNIRAP™ Cable Tie - 675 Lb. Tensile Strength (Partially Coated)

Features

- Stainless Steel Cable Tie - Partially Coated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	PARTIALLY COATED
----------------	------------------

Dimensions

Package Height	1.000 in
Length	15.75 in
Package Weight	1.370 lb.
Dimension - Width mm	15.9 mm
Dimension - Width inch	0.62 in
Package Length	20.250 in
Package Width	5.750 in
Dimension - L Length Overall mm	400 mm
Width	0.62 in
Dimension - Length Overall inch	15.75 in

Dimension - Bundle Diameter Max inch	4.02
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	675
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810647660
Material	304 STAINLESS STEEL
UPC 14 Digit GTIN	00781810647660

Logistics

Pallet Quantity	24000
Carton Quantity	1000

Operational

Operating Temperature Celcius Max	115 °C
Operating Temperature Range Celcius	-40 - 115
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)