



CTSS675500PC304Q, 304 SS Tie, 5" Bundle, Partial Coat

By Burndy
Catalog # [CTSS675500PC304Q](#)

304 Stainless Steel UNIRAP™ Cable Tie - 675 Lb. Tensile Strength (Partially Coated)

Features

- Stainless Steel Cable Tie - Partially Coated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	PARTIALLY COATED
----------------	------------------

Dimensions

Package Height	0.700 in
Length	19.68 in
Package Weight	1.630 lb.
Dimension - Width mm	15.9 mm
Dimension - Width inch	0.62 in
Package Length	25.000 in
Package Width	6.000 in
Dimension - L Length Overall mm	500 mm
Width	0.62 in
Dimension - Length Overall inch	19.68 in

Dimension - Bundle Diameter Max inch	5.04
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	675
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810647677
Material	304 STAINLESS STEEL
UPC 14 Digit GTIN	00781810647677

Logistics

Pallet Quantity	15000
Carton Quantity	500

Operational

Operating Temperature Celcius Max	115 °C
Operating Temperature Range Celcius	-40 - 115
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)