



CTSS700200304L, 304 SS Tie, 700 Lb Tensile, 7.87" Long

By Burndy
Catalog # [CTSS700200304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 700 Lb. Tensile Strength
(Uncoated)



Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Length	7.87 in
Dimension - Width mm	12.7 mm
Dimension - Width inch	0.50 in
Dimension - L Length Overall mm	200 mm
Width	0.5 in
Dimension - Length Overall inch	7.87 in
Dimension - Bundle Diameter Max inch	1.97

Force Related

Rating - Minimum Tensile Strength lbs	700
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651506
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810651506

Logistics

Minimum Pack Quantity	50
Pallet Quantity	57600
Carton Quantity	1600

Operational

Operating Temperature Celcius Max	300 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Fahrenheit	-

Product Assets

[Catalog \[English\]](#)



A Hubbell brand