



CTSS700700304L, 304 SS Tie, 700 Lb
Tensile, 27.56" Long

By Burndy
Catalog # [CTSS700700304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 700 Lb. Tensile Strength
(Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Package Height	1.200 in
Length	27.56 in
Package Weight	3.210 lb.
Dimension - Width mm	12.7 mm
Dimension - Width inch	0.50 in
Package Length	31.500 in
Package Width	5.750 in
Dimension - L Length Overall mm	700 mm
Width	0.5 in
Dimension - Length Overall inch	27.56 in

Dimension - Bundle Diameter Max inch	7.09
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	700 Lb
---------------------------------------	--------

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651551
Material	304 STAINLESS STEEL
UPC 12 Digit	781810651551
UPC 14 Digit GTIN	00781810651551

Logistics

Pallet Quantity	22400
Carton Quantity	700

Operational

Operating Temperature Celcius Max	300 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Fahrenheit	-

Product Assets

[Catalog \[English\]](#)