



CTSS900200304L, 304 SS Tie, 900 Lb
Tensile, 7.87" Long

By Burndy
Catalog # [CTSS900200304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 900 Lb. Tensile
Strength (Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Length	7.87 in
Dimension - Width mm	15.9 mm
Dimension - Width inch	0.62 in
Dimension - L Length Overall mm	200 mm
Width	0.62 in
Dimension - Length Overall inch	7.87 in
Dimension - Bundle Diameter Max inch	1.97

Force Related

Rating - Minimum Tensile Strength lbs	920
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651575
Material	304 Stainless Steel
UPC 12 Digit	781810651575
UPC 14 Digit GTIN	00781810651575

Logistics

Minimum Pack Quantity	50
Pallet Quantity	48000
Carton Quantity	1300

Operational

Operating Temperature Celcius Max	300 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand