



CTSS900300304L, 304 SS Tie, 900 Lb Tensile, 11.71" Long

By Burndy
Catalog # [CTSS900300304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 900 Lb. Tensile Strength (Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Length	11.81 in
Dimension - Width mm	15.9 mm
Dimension - Width inch	0.62 in
Dimension - L Length Overall mm	300 mm
Width	0.62 in
Dimension - Length Overall inch	11.81 in

Dimension - Bundle Diameter Max inch	3.00
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	920
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651582
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810651582

Logistics

Minimum Pack Quantity	50
Pallet Quantity	40000
Carton Quantity	900

Operational

Operating Temperature Celcius Max	300 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand