



CTSS900700304L, 304 SS Tie, 900 Lb
Tensile, 27.56" Long

By Burndy
Catalog # [CTSS900700304L](#)

304 Stainless Steel UNIRAP™ Cable Tie - 900 Lb. Tensile
Strength (Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Package Height	1.250 in
Length	27.56 in
Package Weight	4.000 lb.
Dimension - Width mm	15.9 mm
Dimension - Width inch	0.62 in
Package Length	32.500 in
Package Width	6.000 in
Dimension - L Length Overall mm	700 mm
Width	0.62 in

Dimension - Length Overall	27.56 in
inch	
Dimension - Bundle Diameter	7.09
Max inch	

Force Related

Rating - Minimum Tensile	920
Strength lbs	

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651629
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810651629

Logistics

Minimum Pack Quantity	50
Pallet Quantity	1850
Carton Quantity	500

Operational

Operating Temperature Celcius	300 °C
Max	
Operating Temperature Range	-40 - 300
Celcius	
Operating Temperature Celcius	-40 °C
Min	

Product Assets

[Catalog \[English\]](#)