



CUW26RECG5, Deadend Clamp, #6-2/0 ACSR ASC

By Burndy
Catalog # CUW26RECG5

Copper Deadend



Features

- Copper Deadend
- Accommodates #6-2/0 ACSR, #6-2/0 ASC

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	6 AWG-2/0 AWG
Conductor - ACSR Str Size	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG

Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG-2/0 (6/1) Quail AWG
---------------------------------	--

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	98.6 mm
Dimension - Height inch	3.88 in
Dimension - Height fraction	3-22/25 in
Package Weight	0.000 lb.
Dimension - Width mm	81 mm
Dimension - Width inch	3.19 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	213 mm
Dimension - Width fraction	3-15/79 in
Dimension - Length Overall inch	8.38 in

General

Plated	Y
Material - Hardware	Galvanized Steel
UPC	621945007857
Material	Aluminum Alloy
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00621945007857

Product Assets

[Catalog \[English\]](#)