



CUW30AE, Deadend Clamp, Aluminum Alloy

By Burndy

Catalog # [CUW30AE](#)

Deadend Clamp, High Strength Al Alloy, 1/0 AWG - 300 kcmil Al,
1/0 AWG - 266.8 kcmil ACSR, 10.00" L

Features

- High strength aluminum clamp for deadending primary distribution lines
- Straight-line design with hot stick lifting-eye, pulling-eye
- Captured, angled U-bolts
- Snub-pocket V-shaped, range-taking conductor groove and galvanized steel U-bolts provide high holding strength

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	123.3 (7) kcmil-312.8 (19) kcmil
Conductor - AAAC 6201 Size Range	123.3 (7) kcmil-312.8 (19) kcmil
Conductor - AAAC 6201 Size	• 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil • 246.9 (7) kcmil • 312.8 (19) kcmil
Conductor - AL Str Size	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil
Conductor - AL Str Size Range	1/0 AWG-300 kcmil
Conductor - ACSR Str Size	• 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil



Conductor - ACSR Str Size Range
Conductor - AAAC 5005 Size

- 190.8 (12/7) Dorking kcmil
 - 211.3 (12/7) Cochin kcmil
 - 203.2 (16/9) Brahma kcmil
 - 266.8 (18/1) Waxwing kcmil
- 1/0 (6/1) Raven AWG-266.8 (18/1) Waxwing kcmil
- 123.3 (7) kcmil
 - 155.4 (7) kcmil
 - 195.7 (7) kcmil
 - 246.9 (7) kcmil
 - 312.8 (19) kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	91.2 mm
Dimension - Height inch	3.59 in
Dimension - Height fraction	3-23/39 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.68 in
Package Width	0.000 in
Dimension - L Length Overall mm	254 mm
Dimension - Width fraction	3-8/17 in
Dimension - B Length fraction	3-22/25 in
Dimension - Width mm	88 mm
Dimension - Width inch	3.47 in
Dimension - B Length inch	3.88 in
Dimension - Length Overall inch	10 in

General

Material - Hardware	Galvanized Steel
Plated	N
UPC	781810091807
Material	Aluminum Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810091807

Logistics

Minimum Pack Quantity	10
-----------------------	----

Pallet Quantity 525
Carton Quantity 5

Product Assets

[Catalog \[English\]](#)



A Hubbell brand