



CUW32RE, Deadend Clamp, Aluminum Alloy

By Burndy
Catalog # [CUW32RE](#)



Deadend Clamp, High Strength Al Alloy, 3/0 AWG - 350 kcmil Al, 3/0 AWG - 336.4 kcmil ACSR, 10.00" L

Features

- High strength aluminum clamp for deadending primary distribution lines
- Straight-line design with hot stick lifting-eye, pulling-eye
- Captured, angled U-bolts
- Snub-pocket V-shaped, range-taking conductor groove and galvanized steel U-bolts provide high holding strength

Application

For Aluminum, ACSR, 6201 And 5005, Deadending Primary Distribution Lines

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	195.7 (7) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size Range	195.7 (7) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size	• 195.7 (7) kcmil • 246.9 (7) kcmil • 312.8 (19) kcmil • 394.5 (19) kcmil
Conductor - AL Str Size	• 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Size Range	3/0 AWG-350 kcmil
Conductor - ACSR Str Size	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil

Conductor - ACSR Str Size Range
Conductor - AAAC 5005 Size

- 134.6 (12/7) Leghorn kcmil
- 159 (12/7) Guinea kcmil
- 176.9 (12/7) Dotterel kcmil
- 190.8 (12/7) Dorking kcmil
- 211.3 (12/7) Cochin kcmil
- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 3/0 (6/1) Pigeon AWG-336.4 (26/7) Linnet kcmil
- 195.7 (7) kcmil
- 246.9 (7) kcmil
- 312.8 (19) kcmil
- 394.5 (19) kcmil

Configuration

Connector Type Deadend

Dimensions

Package Height	0.000 in
Dimension - Height mm	103.1 mm
Dimension - Height inch	4.06 in
Dimension - Height fraction	4-3/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.72 in
Package Width	0.000 in
Dimension - L Length Overall mm	267 mm
Dimension - Width fraction	3-29/50 in
Dimension - B Length fraction	4-4/21 in
Dimension - Width mm	91 mm
Dimension - Width inch	3.58 in
Dimension - B Length inch	4.19 in
Dimension - Length Overall inch	10.5 in

General

Material - Hardware	Galvanized Steel
Plated	N
Sub Brand	DEADEND CLAMP

UPC	781810092125
Type	CUW-R-E
Material	Aluminum Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810092125

Logistics	
Minimum Pack Quantity	5

Product Assets

[Catalog \[English\]](#)



A Hubbell brand