



CUW34E, Deadend Clamp, 4/0 Str-500 kcmil Copper

By Burndy
Catalog # [CUW34E](#)

Deadend Clamp, 4/0 Str. - 500, 7-3/8 in L, 4 in Width, Bright Dipped

Features

- High strength, two-bolt
- Single saddle design for short span distribution and strain bus application
- Galvanized steel clevis pin and U-bolts

Application

For Short Span Distribution And Strain Bus Application

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4/0 AWG
	• 250 kcmil
	• 300 kcmil
	• 350 kcmil
	• 400 kcmil
	• 450 kcmil
	• 500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions



Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3 in
Dimension - Height fraction	3
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	187 mm
Dimension - Width fraction	3-81/89 in
Dimension - B Length fraction	2-81/89 in
Dimension - Width mm	99 mm
Dimension - Width inch	3.91 in
Dimension - B Length inch	2.91 in
Dimension - Length Overall inch	7.38 in

General

Product Family	Utility Overhead & Underground Distribution>Dead End Fittings & Accessories
Material - Hardware	Galvanized Steel
Plated	Yes
Sub Brand	DEADEND CLAMP
Product Type	Mechanical
UPC	781810091708
Type	CUW-E
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 14 Digit GTIN	00781810091708

Logistics

Minimum Pack Quantity	1
Pallet Quantity	500
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)