



CUW361RE, Deadend Clamp, Aluminum Alloy

By Burndy
Catalog # [CUW361RE](#)

Deadend Clamp; Aluminum Alloy

Features

- High strength aluminum clamp for deadending primary distribution lines
- Straight-line design with hot stick lifting-eye, pulling-eye
- Captured, angled U-bolts
- Snub-pocket V-shaped, range-taking conductor groove and galvanized steel U-bolts provide high holding strength

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	4/0(6-1 STR) AWG - 477(18-1
Range	STR) kcmil
Conductor - AL Str Size Range	4/0 AWG - 500 kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Dimension - Width inch	3.68 in
Dimension - Width mm	93 mm
Dimension - B Length inch	4.40 in
Dimension - L Length Overall mm	277 mm
Dimension - Height inch	4.12 in
Dimension - Length Overall inch	10.90 in

General

Material	Aluminum Alloy
UPC	781810093016

Logistics

Minimum Pack Quantity	11
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)