



CUW391AE, Deadend Clamp, Aluminum Alloy

By Burndy
Catalog # [CUW391AE](#)

Deadend Clamp; Aluminum Alloy



Features

- High strength aluminum clamp for deadending primary distribution lines
- Straight-line design with hot stick lifting-eye, pulling-eye
- Captured, angled U-bolts
- Snub-pocket V-shaped, range-taking conductor groove and galvanized steel U-bolts provide high holding strength

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	300(26-7 STR) - 636(26-7 STR)
Range	kcmil
Conductor - AL Str Size Range	336.4 - 795 kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Dimension - Width inch	4.12 in
Dimension - Width mm	105 mm
Dimension - B Length inch	5.19 in
Dimension - L Length Overall mm	297 mm
Dimension - Height inch	4.82 in
Dimension - Length Overall inch	11.68 in

General

Material	Aluminum Alloy
UPC	781810093252

Logistics

Minimum Pack Quantity	6
Carton Quantity	5
Pallet Quantity	180

Product Assets

[Catalog \[English\]](#)