



CUW556AE, Deadend Clamp, Aluminum Alloy

By Burndy
Catalog # [CUW556AE](#)

High Strength Aluminium Alloy, Deadend Clamp, 3/0 - 556 kcmil
ACSR, 10.4" Length

Features

- High strength aluminum clamp for deadending primary distribution lines
- Straight-line design with hot stick lifting-eye, pulling-eye
- Captured, angled U-bolts
- Snub-pocket V-shaped, range-taking conductor groove and galvanized steel U-bolts provide high holding strength

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350 • 397.5 • 400 • 450 • 477 • 500 • 550 • 556.5
-------------------------	---



Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	114.3 mm
Dimension - Height inch	4.5 in
Dimension - Height fraction	4-1/2 in
Package Weight	0.000 lb.
Dimension - Width mm	101 mm
Dimension - Width inch	3.97 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	264 mm
Dimension - Width fraction	3-65/67 in
Dimension - Length Overall inch	10.4 in

General

Plated	Y
Material - Hardware	Galvanized Steel
UPC	781810434550
Material	Aluminum Alloy
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810434550

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand