



CY1207L11D13G1TN Rope Lay Braid

By Burndy
Catalog # [CY1207L11D13G1TN](#)

Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	11.13 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	283 mm
mm	
Height	0.94 in
Width	1.69 in
Dimension - Length Overall	11.13 in
inch	
Dimensions	11.13 in x 1.69 in x 0.94 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	29
UPC	781810282519
Material	Copper
UPC 12 Digit	781810282519
UPC 14 Digit GTIN	00781810282519

Logistics

Minimum Pack Quantity	1
Pallet Quantity	324
Carton Quantity	9

Product Assets

[Catalog \[English\]](#)