



# CY2/0L20G2 Rope Lay Braid

By Burndy  
Catalog # [CY2/0L20G2](#)

Rope Lay Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

Certification - CSA Approved      No

## Configuration

Connector Type                      Braid

## Dimensions

|                              |           |
|------------------------------|-----------|
| Package Height               | 0.000 in  |
| Length                       | 20 in     |
| Package Weight               | 0.000 lb. |
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Dimension - L Length Overall | 508 mm    |
| Weight                       | 1.329 lb. |
| Dimension - Length Overall   | 20 inch   |

## General

|                   |                |
|-------------------|----------------|
| UPC               | 621945447424   |
| Material          | Copper         |
| UPC 12 Digit      | 621945447424   |
| UPC 14 Digit GTIN | 00621945447424 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 10  |
| Pallet Quantity       | 720 |
| Carton Quantity       | 10  |

## Product Assets

[Catalog \[English\]](#)