



CY2CL14G12 Flexible Rope Lay Copper Braid

By Burndy
Catalog # [CY2CL14G12](#)

Flexible Rope Lay Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved No

Standards - RoHS Compliance CM
Status

Dimensions

Dimension - L Length Overall	356 mm
mm	
Dimension - Length Overall	14 in
inch	
Length	14 in

General

UPC 621945467880

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalog \[English\]](#)