



CY4/0L22G5TN Rope Lay Braid

By Burndy
Catalog # [CY4/0L22G5TN](#)

Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	335 A
-----------------	-------

Dimensions

Package Height	0.000 in
Length	22 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	559 mm
mm	
Weight	0.288 lb.
Dimension - Length Overall	22 in
inch	

General

UPC	781810668979
Material	Copper
UPC 12 Digit	781810668979
UPC 14 Digit GTIN	00781810668979

Logistics

Minimum Pack Quantity	40
-----------------------	----

Product Assets

[Catalog \[English\]](#)