

CZ11, Grounding Clamp, Cable to Water Pipe

By Burndy
Catalog # [CZ11](#)

Grounding Clamp, Cable to Water Pipe, 10 - 2 AWG, 1/2" - 1" Water
Pipe, W/ zinc plated screws



Features

- Die Cast Zinc with Zinc-plated steel hardware

Application

For Bare Wire

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rigid Pipe Size Range	1/2" - 1"
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - AL Str Size Range	8-2
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Armored Cable Size	N
Conductor - Copper Str Size Range	10 AWG - 2 AWG

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Height mm	40 mm
Dimension - Height inch	1.56 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Width mm	16 mm
Dimension - Width inch	0.63 in
Dimension - Length Overall inch	2.25 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>LC Water Pipe Ground Clamps
Material - Hardware Plated	Zinc Plated Steel No
Sub Brand	DIE CAST CLAMPS
Product Type	Mechanical
UPC	781810142387
Type	Grounding Mechanical
Material	Zinc, Cast
Plating Type	Zinc
UPC 12 Digit	781810142387
UPC 14 Digit GTIN	00781810142387

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12500
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)