



# DUW28, Deadend Strain Clamp, #1 Str-4/0 Str Copper

By Burndy  
Catalog # [DUW28](#)



Cu Deadend Strain Clamp, #1 Str - 4/0 Str Cu

## Features

- High strength, corrosion resistant copper alloy strain clamp
- Three silicon bronze U-bolts
- Single serrated saddle
- Galvanized steel clevis pin

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Conductor

|                                   |                                                                                                                             |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size Range | 1 AWG-4/0 AWG                                                                                                               |
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li></ul> |

## Configuration

|                |         |
|----------------|---------|
| Connector Type | Deadend |
|----------------|---------|

## Dimensions

|                       |          |
|-----------------------|----------|
| Package Height        | 0.000 in |
| Dimension - Height mm | 63.5 mm  |

|                                 |            |
|---------------------------------|------------|
| Dimension - Height inch         | 2.5 in     |
| Dimension - Height fraction     | 2-1/2 in   |
| Dimension - B Length fraction   | 4-14/25 in |
| Package Weight                  | 0.000 lb.  |
| Dimension - Width mm            | 59 mm      |
| Dimension - Width inch          | 2.31 in    |
| Package Length                  | 0.000 in   |
| Package Width                   | 0.000 in   |
| Dimension - L Length Overall mm | 249 mm     |
| Dimension - B Length inch       | 4.56 in    |
| Dimension - Width fraction      | 2-9/29 in  |
| Dimension - Length Overall inch | 9.81 in    |

## General

|                     |                      |
|---------------------|----------------------|
| Plated              | Y                    |
| Material - Hardware | Galvanized Steel     |
| UPC                 | 781810013427         |
| Material            | Copper Alloy         |
| Plating Type        | Tin - Electro Plated |
| UPC 14 Digit GTIN   | 00781810013427       |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 11  |
| Pallet Quantity       | 378 |
| Carton Quantity       | 2   |

## Product Assets

[Catalog \[English\]](#)