




DUW28A, Deadend Strain Clamp without Pulling Eye, Aluminum Alloy

By Burndy

Catalog # [DUW28A](#)

Al Alloy Deadend Strain Clamp, Without Pulling Eye, #1 - 4/0
AWG Al, #2 - 4/0 AWG ACSR



Features

- High strength cast aluminum alloy clamp recommended for strain bus applications
- Three galvanized steel 8_bolts, single saddle, Headed clevis pin providing high holding strength

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size	• 77.47 (7) kcmil • 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - AL Str Size	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - AAAC 5005 Size	• 77.47 (7) kcmil • 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - AL Str Size Range	1 AWG-4/0 AWG
Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penquin AWG

Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-4/0 (6/1) Penquin AWG
---------------------------------	---

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	52.3 mm
Dimension - Hole Size fraction	7/8
Dimension - Height inch	2.06 in
Dimension - Height fraction	2
Dimension - B Length fraction	5-4/21 in
Package Weight	0.000 lb.
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	1.44 in
Dimension - L Length Overall mm	264 mm
Dimension - B Length inch	5.19 in
Dimension - Width fraction	2-1/4 in
Dimension - Hole Size mm	22 mm
Dimension - Hole Size inch	0.88 in
Dimension - Length Overall inch	10.41 in

General

Plated	N
Material - Hardware	Galvanized Steel
UPC	781810013366
Prefilled Oxide Inhibitor	N
Material	Aluminum Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810013366

Logistics

Minimum Pack Quantity	14
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand