

DUW31, Deadend Clamp, Copper Alloy

By Burndy
Catalog # [DUW31](#)



Copper Alloy Deadend Clamp

Features

- High strength, corrosion resistant copper alloy strain clamp
- Three silicon bronze U-bolts
- Single serrated saddle
- Galvanized steel clevis pin

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	4/0 AWG-350 kcmil
Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	49.3 mm

Dimension - Height inch	1.94 in
Dimension - Height fraction	1-47/50 in
Dimension - B Length fraction	4-14/25 in
Package Weight	0.000 lb.
Dimension - Width mm	62 mm
Dimension - Width inch	2.44 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	249 mm
Dimension - B Length inch	4.56 in
Dimension - Width fraction	2-11/25 in
Dimension - Length Overall inch	9.81 in

General

Plated	Y
Material - Hardware	Galvanized Steel
UPC	781810013434
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810013434

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)