



EA28, Heavy Duty Rotational Copper Lug Connector

By Burndy
Catalog # [EA28](#)

Cu Alloy VERSILUG Terminal, 1/0-4/0 AWG Str., Adjustable Clamping Element to Allow a Variety of Angles



Features

- Type EA VERSILUG™ is a compact, high copper alloy terminal for joining cable to equipment pads or bar
- Clamping element is adjustable to several angles
- One-wrench installation

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bars

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Size	1/0-4 AWG
Number Of Conductors	1
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	1/0 -4/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Clamping Elements	1
Connector Type	Rotational Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width fraction	1-1/16 in
Dimension - Pad Width inch	1.06 in
Package Height	0.000 in
Dimension - Height mm	44.5 mm
Dimension - Hole Size fraction	7/16
Dimension - Height inch	1.75 in
Dimension - Height fraction	1-3/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.44 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	1-11/25 in
Dimension - B Length inch	1.44 in
Dimension - N inch	0.53 in
Dimension - Length Overall inch	3.19 in

Force Related

Installation Torque Recommended in-lb	250 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	VERSILUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	VERSILUG
Product Type	Terminal
UPC	781810326305
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810326305
UPC 14 Digit GTIN	00781810326305

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	9

Operational



A Hubbell brand