



Electric Hydraulic Pump, 1/2 HP, Reservoir Volume 2 qts, 10000 psi, 115V AC/60Hz

By Burndy
Catalog # [EPP10](#)

EPP Series Pump, 1/2HP 115VAC/60Hz



Features

- Lightweight
- Small size
- Factory set relief valve
- 100,000 (+) life cycles
- Sealed electric pendant switch

Application

Pumping

Specifications

Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes

Current

Current Draw Max	12.5 Amperes
------------------	--------------

Dimensions

Length	16 in
Weight	30 lb.
Height	8 in

Width	6 in
Dimensions	16 in x 6 in x 8 in

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Tool Type	Pump, Electric Hydraulic
UPC	781810033456
Type	Pumps
UPC 12 Digit	781810033456
UPC 14 Digit GTIN	00781810033456

Logistics

Package Contents	Pump only
------------------	-----------

Operational

Power Source	• 1/2 HP 115V-AC • 60 Cycle
--------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)