



ES25A2W, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES25A2W](#)



BURNDY® INSULINK™ Service Entrance Sleeve

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripealed to limit oxidation and increase life of the connection

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size B	• 4 AWG • 3 AWG
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Solid Size B	2 AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	• 4 AWG • 3 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B Range	4 AWG-3 AWG
Conductor - ACSR Str Size B	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - Copper Str Size B Range	4 AWG-3 AWG

Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
-----------------------------------	--------------------------------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	70 mm
Dimension - Outside Diameter inch	.75 in
Dimension - Length Overall inch	2.75 in

General

Plated	Y
Insulation Type	Nylon
Trade Name	INSULINK™
Die Index	BG or 5/8
UPC	781810000373
Color Code - Side B	Orange
Color Code - Side A	Yellow
Type	Insulated Service Entrance Connectors
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810000373
UPC 14 Digit GTIN	00781810000373

Logistics

Pallet Quantity	24000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)