



ES25A4W, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # ES25A4W

BURNDY® INSULINK™ Service Entrance Sleeve

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripealed to limit oxidation and increase life of the connection

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size B	• 6 AWG • 5 AWG
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Solid Size B	4 AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	• 6 AWG • 5 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B Range	6 AWG-5 AWG
Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - Copper Str Size B Range	6 AWG-5 AWG

Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG
-----------------------------------	--------------------

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Outside Diameter inch	.75 in
Dimension - Length Overall inch	2.75 in

General

Plated	Y
Insulation Type	Nylon
Trade Name	INSULINK™
Die Index	BG or 5/8
UPC	781810097977
Color Code - Side B	Blue
Color Code - Side A	Yellow
Type	Insulated Service Entrance Connectors
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810097977
UPC 14 Digit GTIN	00781810097977

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)