



ES25R25RG1, Service Entrance Sleeve Kit, contains 2 Insulated Sleeves, 1 Uninsulated Compression Sleeve

By Burndy
Catalog # [ES25R25RG1](#)

BURNDY® INSULINK™ Service Entrance Sleeve Kit

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	70 mm
mm	

Dimension - Outside Diameter	.75 in
inch	
Dimension - Length Overall	2.75 in
inch	

General

Plated	Y
Insulation Type	Nylon
Die Index	BG
UPC	781810087794
Type	Insulated Service Entrance Connectors
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810087794
UPC 14 Digit GTIN	00781810087794

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4500
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)