



BURNDY

ES2W2WBOX, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy

Catalog # [ES2W2WBOX](#)

BURNDY® INSULINK™ Service Entrance Sleeve



Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

Specifications

Certification - ETL

No

Certification - UL Recognized

No

Standards - RoHS Compliance Status
CM
Certification - cULus
No
UL Listed
No
Certification - CSA Approved
No

Conductor

Conductor - Copper Str Size A
3 STR,4 STR, 2 SOL
Conductor - Copper Str Size B
3 STR,4 STR, 2 SOL
Conductor - AL Str Size A
3 STR,4 STR, 2 SOL
Conductor - AL Str Size B
3 STR,4 STR, 2 SOL
Conductor - ACSR Str Size A
4 AWG
Conductor - ACSR Str Size B
4 AWG

Dimensions

Package Height
0.000 in
Package Weight
0.000 lb.
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
70 mm
Dimension - Outside Diameter inch
.75 in
Dimension - Length Overall inch
2.75 in

General

Plated
Y
Insulation Type
Nylon
Trade Name
INSULINK™
Die Index
BG
UPC
781810085028
Type
Insulated Service Entrance Connectors
Prefilled Oxide Inhibitor
Y
Insulation
Y
Material
Aluminum
Plating Type
Unplated
UPC 12 Digit
781810085028
UPC 14 Digit GTIN
00781810085028

Logistics

Minimum Pack Quantity
96
Pallet Quantity
11136
Carton Quantity
24

Product Assets



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-ES2W2WBOX-SPEC-EN | REV 5/2026