



**Oh No!**  
IMAGE COMING SOON

FQN10F25X03B, Nylon Fully Insulated  
Female Quick Disconnect, 10-12 AWG,  
NEMA Tab Size: .250 X .032

By Burndy  
Catalog # [FQN10F25X03B](#)

MATERIAL: TIN-PLATED BRASS. 300 VOLTS MAX. 105 C MAX.

Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - ETL                | No    |
| Certification - UL Recognized      | N     |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM    |
| Certification - cULus              | Y     |
| Industry Standard(s)               | UL467 |
| UL Listed                          | No    |
| Certification - CSA Approved       | No    |

Conductor

|                                     |                                                                       |
|-------------------------------------|-----------------------------------------------------------------------|
| Conductor Size                      | 12 - 10 AWG                                                           |
| Conductor - Copper Solid Size Range | N/A                                                                   |
| Conductor Type                      | CU C Str-Size                                                         |
| Conductor - Copper Str Size Range   | 12 AWG-10 AWG                                                         |
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>12 AWG</li><li>10 AWG</li></ul> |

Configuration

|                |                         |
|----------------|-------------------------|
| Connector Type | Female Quick Disconnect |
|----------------|-------------------------|

Dimensions

|                |          |
|----------------|----------|
| Package Height | 0.000 in |
|----------------|----------|

|                                           |           |
|-------------------------------------------|-----------|
| Package Weight                            | 0.000 lb. |
| Dimension - Width inch                    | 0.26 in   |
| Package Length                            | 0.000 in  |
| Dimension - F Width Center to Center inch | 0.13 in   |
| Package Width                             | 0.000 in  |
| Dimension - Thread Size                   | -         |
| Dimension - Length Overall inch           | 0.98 in   |

General

|                   |                       |
|-------------------|-----------------------|
| Plated            | Y                     |
| Insulation Type   | Nylon                 |
| Trade Name        | FINGRIP               |
| UPC               | 781810292631          |
| Type              | Disconnect Connectors |
| Insulation        | Y                     |
| Material          | Brass                 |
| Plating Type      | Tin                   |
| UPC 12 Digit      | 781810292631          |
| UPC 14 Digit GTIN | 00781810292631        |

Logistics

|                 |       |
|-----------------|-------|
| Pallet Quantity | 99999 |
| Carton Quantity | 500   |

Product Assets

[Catalog \[English\]](#)