



Oh No!
IMAGE COMING SOON

FQN14M25X03B, Nylon Fully Insulated
Male Quick Disconnect, 14-16 AWG, NEMA
Tab Size: .250 X .032

By Burndy
Catalog # [FQN14M25X03B](#)

MATERIAL: TIN-PLATED BRASS. 300 VOLTS MAX. 105 C MAX.

Specifications

Certification - ETL	No
Certification - UL Recognized	N
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size Range	N/A
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG 14 AWG

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Dimension - Width inch	0.25 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.08 in
Package Width	0.000 in
Dimension - Thread Size	-
Dimension - Length Overall inch	0.98 in

General

Plated	Y
Insulation Type	Nylon
Trade Name	FINGRIP
UPC	781810292600
Type	Disconnect Connectors
Insulation	Y
Material	Brass
Plating Type	Tin
UPC 12 Digit	781810292600
UPC 14 Digit GTIN	00781810292600

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)



A Hubbell brand