



# FQN18F25X03D, Nylon Female Disconnect, 22-18 AWG (.25 x .03)

By Burndy  
Catalog # [FQN18F25X03D](#)

Fully Insulated Nylon Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

## Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

## Application

For quickly connecting or disconnecting a terminal

## Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - UL Recognized      | No    |
| Certification - cULus              | Yes   |
| Industry Standard(s)               | UL467 |
| Certification - ETL                | No    |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance        | CM    |
| Status                             |       |
| UL Listed                          | No    |
| Certification - CSA Approved       | No    |

## Conductor

|                                   |                                                                       |
|-----------------------------------|-----------------------------------------------------------------------|
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>20 AWG</li><li>18 AWG</li></ul> |
| Conductor Size                    | 22 - 18 AWG                                                           |
| Conductor Type                    | CU C Str-Size                                                         |
| Conductor - Copper Str Size Range | 20 AWG - 18 AWG                                                       |

## Configuration

|                |                         |
|----------------|-------------------------|
| Connector Type | Female Quick Disconnect |
|----------------|-------------------------|

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 300 V |
|-------------------|-------|



## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - Strip Length inch   | 3/8 in    |
| Dimension - Width mm            | 6 mm      |
| Dimension - Width inch          | 0.25 in   |
| Dimension - Length Overall inch | 0.90 in   |

## General

|                   |                       |
|-------------------|-----------------------|
| Product Family    | COMPRESSION           |
| Insulation Type   | Nylon                 |
| Trade Name        | FINGRIP™              |
| Insulation        | Y                     |
| Plated            | Yes                   |
| Sub Brand         | FINGRIP               |
| Product Type      | Terminal              |
| UPC               | 781810293010          |
| Type              | Disconnect Connectors |
| Material          | Brass                 |
| Plating Type      | Tin                   |
| UPC 12 Digit      | 781810293010          |
| UPC 14 Digit GTIN | 00781810293010        |

## Logistics

|                 |       |
|-----------------|-------|
| Pallet Quantity | 99999 |
| Carton Quantity | 600   |

## Product Assets

[Catalog \[English\]](#)