



FQP18F25X03D, Fully Insulated Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [FQP18F25X03D](#)



Fully Insulated Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

General

Catalog Number	FQP18F25X03D
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292952
UPC 14 Digit GTIN	00781810292952

Dimensions

Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
-----------------------------	---------------

Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

- [3D Models - FQP18F25X03D_MODEL-PDF](#)
- [3D Models - FQP18F25X03D_MODEL-STEP](#)
- [3D Models - FQP18F25X03D_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094208](#)
- [Specifications - FQP18F25X03D](#)