



GA25H29TN, Mech Ground Conn for Cu Cable to H-Beam, Tinned

By Burndy
Catalog # [GA25H29TN](#)

Mechanical Ground Connector for Copper Cable to "H" Beam



Features

- High copper alloy ground connector, Tin plated
- Joins wide range of cable parallel to "H" beams or square tube
- Silicon bronze for superior corrosion protection

Specifications

Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size	250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	4.75 in
Dimension - Height fraction	4-3/4 in
Package Weight	0.000 lb.

Dimension - Width mm	102 mm
Dimension - Width inch	4 in
Package Length	0.000 in
Package Width	0.000 in

Force Related

Installation Torque	240 Lb in
Recommended Run in-lb	

General

Plated	Y
UPC	621945462724
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810415146
UPC 14 Digit GTIN	00781810415146

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)