

GAR1426SE, Mech Ground Conn, Cable to Rod or Pipe

By Burndy

Catalog # [GAR1426SE](#)



To Rod or Pipe with the Same Connector.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Rebar Size	7 8
Conductor - Rebar Size Range	7-8
Conductor - Copper Solid Size	4 3 2 1 1/0 2/0 3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Rod Size Range	7/8-1
Conductor Type	- CU C Solid-Size - CU C Str-Size - CU Tube Std-Size - Rod-Size
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Str Size	5 4 3 2 1 1/0 2/0
Conductor - Rod Size	7/8

Conductor - Copper Tube Std Size Range	1/2-3/4
Conductor - Copper Tube Std Size	1/2 3/4

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Package Weight	0.000 lb.
Dimension - Width mm	60 mm
Dimension - Width inch	2.38 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	1.50 in
Dimension - Outside Diameter inch	1.05 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810117194
U Bolt Type	249
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810117194
UPC 14 Digit GTIN	00781810117194

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)