



GAR1428CG1, Mech Ground Conn, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1428CG1](#)

Mechanical Ground Connector



Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	3/4" IPS to 2/0
----------------------------	-----------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Force Related

Installation Torque Recommended in-lb	170
---------------------------------------	-----

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945011946
U Bolt Type	249
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945011946
UPC 14 Digit GTIN	00621945011946

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)