



GAR1526W, Mech Ground Conn, Cable to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GAR1526W](#)



To Rod or Pipe with the Same Connector.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Rebar Size	• 9 • 10
Conductor - Pipe or Round Tube Size Range	1 in
Conductor - Rebar Size Range	9-10
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Rod Size Range	1 1/8-1 1/4
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	5 AWG - 1/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Rod Size	1.120-1.31 in
Conductor - Copper Tube Std Size Range	1
Conductor - Copper Tube Std Size	1

Dimensions

Package Height	0.000 in
Dimension - Height mm	73.2 mm
Dimension - Height inch	2.88 in
Package Weight	0.000 lb.
Dimension - Width mm	67 mm
Dimension - Width inch	2.62 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	1.75 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	
Installation Torque	240 Lb in
Recommended Run in-lb	

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810117088
U Bolt Type	244
Material	Copper
Plating Type	Tin Plated bodies and electro tin plated hardware
UPC 12 Digit	781810117088
UPC 14 Digit GTIN	00781810117088

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)