



GAR1528CG4, Mech Ground Conn, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1528CG4](#)



To Rod or Pipe with the Same Connector.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size Range	1 in
Conductor - Copper Solid Size	4/0
Conductor - Copper Solid Size Range	4/0
Conductor - AL Str Size	2/0-4/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	2/0 AWG - 4/0 AWG
Conductor - Copper Str Size	2/0-4/0 AWG
Conductor - Copper Tube Std Size Range	1
Conductor - Copper Tube Std Size	1

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	28 mm
Dimension - B Length inch	1.12 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Length Overall inch	1.12 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
Installation Torque Recommended Run in-lb	480 Lb in

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945012004
U Bolt Type	311
Material	Copper
Plating Type	Tin plated
UPC 12 Digit	621945012004
UPC 14 Digit GTIN	00621945012004

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[Catalog \[English\]](#)