



GAR1626G1TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plate

By Burndy
Catalog # [GAR1626G1TN](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, #4 Sol-2/O Str Cu, 1-1/4" IPS, 1-3/8" to 1-1/2" Rod



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size Range	1-1/4 in
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Size	2/O AWG

Conductor - Rod Size	1.380-1.66 in
----------------------	---------------

Force Related

Installation Torque	240 Lb in
Recommended Run in-lb	

General

Plated	Y
UPC	781810541234
Material	Copper
Plating Type	Tin plated
UPC 12 Digit	781810541234
UPC 14 Digit GTIN	00781810541234

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)