



GAR1626TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GAR1626TN](#)



To Rod or Pipe with the Same Connector.

Features

- Wire to Rebar
- Fence Post Grounding Connector
- Wire to Pipe
- One-wrench installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for US and Canadian Markets
- Select connectors qualified to IEEE-837-2014

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rebar Size	11
Conductor - Pipe or Round Tube Size Range	1-1/4 in
Conductor - Rebar Size Range	11
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Rod Size Range	1 1/2-1 5/8
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Rod Size	1.380-1.66 in
Conductor - Copper Tube Std Size Range	1 1/4

Conductor - Copper Tube Std Size 1 1/4

Dimensions

Package Height	0.000 in
Dimension - Height mm	88.9 mm
Dimension - Height inch	3.50 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	1.88 in
Dimension - Outside Diameter inch	1.66 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	
Installation Torque	240 Lb in
Recommended Run in-lb	

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945144996
U Bolt Type	204
Material	Copper
Plating Type	Tin plated
UPC 12 Digit	621945144996
UPC 14 Digit GTIN	00621945144996

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand