

GAR1729TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plate

By Burndy
Catalog # [GAR1729TN](#)



To Rod or Pipe with the Same Connector.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size Range	1-1/2 in
Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Rod Size Range	1 5/8-1 7/8
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Str Size	250 Kcmil
Conductor - Rod Size	1.620-1.90 in
Conductor - Copper Tube Std Size Range	1 1/2
Conductor - Copper Tube Std Size	1 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	101.6 mm
Dimension - Height inch	4.00 in
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - B Length inch	2.31 in
Dimension - Outside Diameter inch	1.90 in
Dimension - Length Overall inch	1.81 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	
Installation Torque	240 Lb in
Recommended Run in-lb	

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810246887
U Bolt Type	268
Material	Copper
Plating Type	Tin plated
UPC 12 Digit	781810246887
UPC 14 Digit GTIN	00781810246887

Logistics

Pallet Quantity	1152
Carton Quantity	36

Product Assets

[Catalog \[English\]](#)