

GAR174CW, Mech Ground Conn, Cable to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GAR174CW](#)



Ground Clamp Copper Tin Plated bodies and electro tin plated hardware 8 AWG-4 AWG Installation Torque Recommended Run in-lb 240 LB in

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size Range	1-1/2 in
Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8-3
Conductor - Rod Size Range	1 5/8-1 7/8
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Rod Size	1.620 in-1.90 in
Conductor - Copper Tube Std Size Range	1 1/2
Conductor - Copper Tube Std Size	1 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	101.6 mm
Dimension - Height inch	4.00 in
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - B Length inch	2.31 in
Dimension - Outside Diameter inch	1.90 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
Installation Torque Recommended Run in-lb	240 Lb-in

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810106846
U Bolt Type	268
Material	Copper
Plating Type	Tin Plated bodies and electro tin plated hardware
UPC 12 Digit	781810106846
UPC 14 Digit GTIN	00781810106846

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)