



GAR1828CG3, Mech Ground Conn, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1828CG3](#)

To Rod or Pipe with the Same Connector.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	4/0
Conductor - Copper Solid Size Range	4/0
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	2/0 AWG - 4/0 AWG
Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Tube Std Size Range	2
Conductor - Copper Tube Std Size	2

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	103 mm
Dimension - Width inch	4.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	28 mm
Dimension - B Length inch	1.12 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Length Overall inch	1.12 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945138254
U Bolt Type	260
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945138254
UPC 14 Digit GTIN	00621945138254

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalog \[English\]](#)