



GAR1829G1TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plate

By Burndy
Catalog # [GAR1829G1TN](#)

Ground Clamp Copper Tin plated 2/0 AWG-250 kcmil Installation
Torque Recommended Run in-lb 240 LB in



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round	2 in
Tube Size Range	
Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Str Size	250 Kcmil

Conductor - Rod Size	2 in-2.38 in
----------------------	--------------

Force Related

Installation Torque	240 Lb-in
Recommended Run in-lb	

General

Plated	Y
UPC	781810541210
Material	Copper
Plating Type	Tin plated
UPC 12 Digit	781810541210
UPC 14 Digit GTIN	00781810541210

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)