

GAR194C, Mech Grounding Connector, Cable to Rod or Pipe

By Burndy

Catalog # [GAR194C](#)

Ground Clamp Copper 8 AWG-4 AWG Installation Torque
Recommended Run in-lb240 LB in



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod
Or Tube, Direct Burial Cable, Fence Post

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size Range	2-1/2 in
Conductor - Rod Size Range	2 1/2 in-2 7/8 in
Conductor - Copper Str Size	4 AWG
Conductor - Rod Size	2.5 in-2.88 in
Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8 AWG-3 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor - Copper Tube Std Size	2 1/2 IPS IPS

Dimensions

Package Height	0.000 in
Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Dimension - Height fraction	5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Outside Diameter inch	2.88 in
Dimension - Width fraction	4-1/4 in
Dimension - Width mm	106 mm
Dimension - Width inch	4.19 in
Dimension - B Length inch	3.25 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	
Installation Torque	240 Lb-in
Recommended Run in-lb	

General

Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810235607
Type	GAR
U Bolt Type	266
Material	Copper
Plating Type	Bright Dipped
UPC 12 Digit	781810235607
UPC 14 Digit GTIN	00781810235607

Logistics

Pallet Quantity	1300
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)