



GAR194CW, Mech Ground Conn, Cable to Rod or Pipe, Tin Plated

By Burndy

Catalog # [GAR194CW](#)

Copper Cable Connection to Rod or Pipe with the Same Connector, Tin Plated



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	2 1/2 in
Conductor - Copper Solid Size	• 8 • 7 • 6 • 5 • 4 • 3
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Rod Size Range	2 1/2-2 3/4
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Str Size	• 9 • 8 • 7 • 6 • 5 • 4

Conductor - Rod Size	2.5 - 2.88 in
Conductor - Copper Tube Std Size Range	2 1/2
Conductor - Copper Tube Std Size	2 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Package Weight	0.000 lb.
Dimension - Width mm	106 mm
Dimension - Width inch	4.19 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - B Length inch	3.25 in
Dimension - Outside Diameter inch	2.88 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810114100
U Bolt Type	266
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810114100
UPC 14 Digit GTIN	00781810114100

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand